

# simalube IMPULSE connect

## Pressure booster for the simulube lubricator



The **simalube IMPULSE** connect is the latest generation of the pressure booster from the simalube family. The proven functions of the IMPULSE have been supplemented with the option of connecting the device to a smartphone via **Bluetooth®**. In connection with the newly developed **«simatec world of maintenance» app**, the devices can be easily configured and then monitored without having to be directly at the lubrication point. Information such as general status, fill level, lubricant, size, start and change date etc. is displayed to the user and easy to read in the app.

#### **Description simalube IMPULSE connect**

- Pressure booster simalube IMPULSE
- 2 Battery pack
- 3 Function display LED (green/red/blue)
- 4 Connection thread G ¼"







#### **Technical Information simulube IMPULSE connect**

simalube IMPULSE	Automatic pressure booster for the simalube lubricator	
Drive system	Electromechanical	
Power supply	Battery pack 6 V 2.3 Ah (Alkaline)	
Function display	LED status display – green/red/blue every 10 seconds	
Connectivity	IMPULSE connect supports Bluetooth® Low Energy 5.0 standard. The connection can reach up to 20 m in an interference free, open-field environment.	
Dispensing volume	Approx. 0.5 ml per stroke (Impulse)	
Working pressure	Up to 10 bar	
Operating temperature	−10 °C to +55 °C	
Time setting	1 to 12 months – determined by the setting on the simalube "Automatic" mode or the "Time" mode preselected by the app.	
Lubrication rate	Depends on the size and settings of the simalube: 0.17 to 8.3 ml/day	
Lubricator volume	According to lubricator: 60 ml, 125 ml, 250 ml	
Lubricant	Greases up to NLGI 2 or oils	
Installation position	Any	
Connection thread	G ¼" (with integrated non-return valve)	
Housing dimensions	Ø 60 × 93 mm	
Housing material	PET semitransparent	
Weight	0,26 kg	
Protection rating	IP68 (dust and water resistant)	
Warranty & period of use	3 years from the production date or until 10 simalube lubricators (125ml) have been emptied	
Storage	Recommended at +20 °C (+/-5 °C)/+68 °F (+/-41 °F). Protect against sunlight and store in a dry place (<65 % humidity)	

### Dimensions and disposal of the simalube IMPULSE connect



	mm	inch
а	G ¼''	
b	Ø60	Ø2.36
C	10	0.39
d	8	0.31
е	<i>7</i> 5	2.95
f	130	5.12
g	169	6.65
h	262	10.31

Dispose the battery pack in battery recycling

Download the new simatec app «simatec world of maintenance»:







Download on the App Store







Dispose according 2012/19/EU (WEEE)

#### simatec ag

Stadthof 2 CH-3380 Wangen a. Aare Tel.: +41 (0)32 636 50 00 welcome@simatec.com www.simatec.com

